Product data sheet

Specifications





19" fixed chassis 12U forPLA enclosure H750xW750mm

NSYBRF12PLAG

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 187.83 USD

Main

| Range | Thalassa |
|---------------------------------------|--|
| Accessory / Separate Part Category | Mounting accessory |
| Product Or Component Type | 19" rack |
| Application | Multi-purpose |
| For Enclosure Nominal Dimensions | - |
| Rack Type | Fixed |
| Mounting Location | Front of enclosure |
| Range Compatibility | Thalassa Thalassa PLA Thalassa Thalassa PHD |
| Device Composition | fixing elements 2 19" uprights |
| Quantity Per Set | Set of 1 |
| Number Of Units 19" | 12 |

Complementary

| - | |
|----------------------------|-----------------------------|
| Material | sheet steel |
| Surface Finish | Epoxy-polyester powder |
| Lock Type | Lock 5 mm double bar |
| Fixing Mode | By fixing element |
| Color | Gray RAL 7035) |
| Permanent Permissible Load | 6.61 lb(US) (3 kg) per unit |
| Height | Nominal 29.53 in (750 mm) |
| Thickness | 0.08 in (2 mm) |

Ordering and shipping details

| Category | US10ES180034 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606485405490 |
| Returnability | No |
| Country Of Origin | ES |

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 31.30 in (79.5 cm) |
| Package 1 Width | 4.33 in (11.0 cm) |
| Package 1 Length | 3.94 in (10.0 cm) |
| Package 1 Weight | 8.50 lb(US) (3.857 kg) |



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |