Product data sheet

Specifications






Signalling beacon adapter, square 80 mm RAL 7040. For S3CM HMI encl.

NSYCMACS80

! Discontinued on: Jan 2, 2024



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Adaptor for signalling beacon	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	sions -	
Mounting Location	On fixed brackets	
Mounting Support	For 80 mm square tube Option of passing cables through the inside Signalling beacon	
Range Compatibility	Spacial Spacial S3CM	
Device Composition	1 adaptor 1 nut	
Quantity Per Set	Set of 1	

Complementary

Material	Adaptor aluminium	
Color	Adaptor Gray RAL 7040)	
Surface Finish	Epoxy-polyester powder	
Fixing Mode	Direct fixing - on fixed brackets of enclosure	
Permanent Permissible Load	0.18 lb(US) (0.08 kg)	
Height	0.00 in (0 mm)	
Diameter	0.55 in (14 mm)	
Net Weight	0.33 lb(US) (0.15 kg)	

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480213250
Returnability	No
Country Of Origin	DE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	6.10 in (15.5 cm)
Package 1 Length	5.98 in (15.2 cm)
Package 1 Weight	5.29 oz (150.0 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations