# Product data sheet





## Fixing sloping on enclosure, square 80 mm. for SPACIAL S3CM HMI encl.

NSYCMUCP80

! Discontinued on: Apr 19, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	Spacial	
Accessory / Separate Part Category	Cable management accessory	
Product Or Component Type	Bent and rotating enclosure fixing	
Device Application	e Application Multi-purpose	
Enclosure Nominal Dimensions	-	
ounting Location On enclosure		
Mounting Support	On enclosures with a depth of 300 mm requires an adaptor For 80 mm square tube On enclosures with depths of 200 and 250 mm	
Range Compatibility	Spacial Spacial S3CM	
Device Composition	fixing elements 1 tilting fixing	
Quantity Per Set	Set of 1	

### Complementary

Material	aluminium
Color	Gray RAL 7040)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By fixing element
Operating Angle	30 °
Permanent Permissible Load	6.83 lb(US) (3.1 kg)
Height	7.17 in (182 mm)
Width	3.94 in (100 mm)
Depth	3.94 in (100 mm)
Net Weight	7.05 lb(US) (3.2 kg)

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480213083
Returnability	No

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.31 in (13.5 cm)
Package 1 Width	6.30 in (16.0 cm)
Package 1 Length	8.27 in (21.0 cm)
Package 1 Weight	7.05 lb(US) (3.2 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations