Product data sheet

Specifications





Adaptation piece for fixing sloping.

NSYCMUCPAD87

() Discontinued on: Apr 19, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

① Discontinued

Main

Range	Spacial
Accessory / Separate Part Category	Cable management accessory
Product Or Component Type	Bent and rotating enclosure fixing
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Between tilting fixing and the enclosure
Mounting Support	For 80 mm square tube On enclosures with a depth of 300 mm
Range Compatibility	Spacial Spacial S3CM
Device Composition	1 adaptor part
Quantity Per Set	Set of 1

Complementary

Material	extruded steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By fixing element
Permanent Permissible Load	0.00 lb(US) (0 kg)
Height	2.48 in (63 mm)
Width	5.91 in (150 mm)
Depth	6.10 in (155 mm)
Diameter	3.15 in (80 mm)
Net Weight	1.10 lb(US) (0.5 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480213076
Returnability	No
Country Of Origin	ES

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.48 in (6.3 cm)
Package 1 Width	5.91 in (15.0 cm)
Package 1 Length	6.10 in (15.5 cm)
Package 1 Weight	17.64 oz (500.0 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations