Product data sheet







Articulated fixing, square 50 mm, cast steel RAL 7040. For S3CM HMI encl.

NSYCMUMA50

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 644.96 USD

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Fixing on support	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	Dimensions -	
Mounting Location	Between tube and support	
Mounting Support	Option of passing cables through the inside For 50 mm square tube	
Range Compatibility	Spacial Spacial S3CM	
Device Composition	fixing elements 1 bellow 1 fixing and rotating bracket	
Quantity Per Set	Set of 1	

Complementary

•	
Material	moulded steel
Color	Bracket Gray RAL 7040) Bellow Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By fixing element M12 - horizontal tube By 4 screws M11 - on support
Operating Angle	170 °
Permanent Permissible Load	9.59 lb(US) (4.35 kg)
Height	5.83 in (148 mm)
Width	5.83 in (148 mm)
Depth	8.27 in (210 mm)
Net Weight	10.14 lb(US) (4.6 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606490213021

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	DE

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.09 in (18.0 cm)
Package 1 Width	9.84 in (25.0 cm)
Package 1 Length	9.84 in (25.0 cm)
Package 1 Weight	10.32 lb(US) (4.682 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	20
ackage 2 Height 19.29 in (49.0 cm)	
Package 2 Width 39.37 in (100.0 cm)	
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	235.89 lb(US) (107.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations