Product data sheet

Specifications





ClimaSys PTC heating resistance 20W, 110-250V

NSYCR20WU2

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 56.06 USD

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Resistance heater
Power Range	20 W
Input Voltage	110250 V AC 50/60 Hz
Electrical Connection	Cable 2 x 0.75 mm² 11.81 in (300 mm)

Complementary

oompromontal y		
Operating Position	Vertical	
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)	
Ip Degree Of Protection	IP20	
Product Certifications	UL VDE	
Material	Body extruded aluminium	
Height	External 3.35 in (85 mm)	
Width	External 0.98 in (25 mm)	
Depth	External 2.24 in (57 mm)	
Condition Of Use	Air sealed enclosure Heaters must be installed with a thermal controller Electrical protection is needed	
Fixing Mode	By clips	
Mounting Support	35 mm DIN rail	

Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480152139	
Returnability	Yes	
Country Of Origin	US	

Packing Units

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Height	2.76 in (7.000 cm)
Package 1 Width	3.15 in (8.000 cm)
Package 1 Length	4.33 in (11.000 cm)
Package 1 Weight	5.71 oz (162.000 g)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations