Product data sheet

Specifications





35mm symetrical DIN rail -L 480mm for using with NSYTCSxx in PLM75

NSYCS500PLM

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 6.22 USD

Main

Anwendung	Multi-purpose
Range	Spacial
Product Or Component Type	Rail
Accessory / Separate Part Category	Mounting accessory
Type Of Rail	Symmetrical DIN
Enclosure Nominal Dimensions	-
Mounting Support	Plastic nut
Range Compatibility	Thalassa Thalassa PLM
Device Composition	1 rail
Quantity Per Set	Set of 2

Complementary

Material	steel
Surface Finish	Zinc coated
Fixing Mode	By fixing element - rear of enclosure
Adjustment	DIN rail adjustment in height, pitch 25 mm
Length	20.08 in (510 mm)
Height	1.38 in (35 mm)
Width	0.28 in (7.2 mm)
Thickness	0.04 in (1 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480191664
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	0.39 in (1.000 cm)
Package 1 Width	1.38 in (3.500 cm)
Package 1 Length	20.08 in (51.000 cm)
Package 1 Weight	6.30 oz (178.500 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	0.79 in (2.000 cm)
Package 2 Width	1.57 in (4.000 cm)
Package 2 Length	20.08 in (51.000 cm)
Package 2 Weight	12.66 oz (359.000 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	20
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	15.75 in (40.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	9.35 lb(US) (4.240 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations