# **Product data sheet**

Specifications



## 35mm symetrical DIN rail -L 795mm for using with NSYTCSxx in PLM108

NSYCS800PLM

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 10.18 USD

#### Main

Anwendung	Multi-purpose	
Range	Spacial	
Product Or Component Type	Rail	
Accessory / Separate Part Category	Mounting accessory	
Type Of Rail	Symmetrical DIN	
Enclosure Nominal Dimensions	-	
Mounting Support	Plastic nut	
Range Compatibility	Thalassa Thalassa PLM	
Device Composition	1 rail	
Quantity Per Set	Set of 2	

### Complementary

•	<del>-</del>
Material	steel
Surface Finish	Zinc coated
Fixing Mode	By fixing element - rear of enclosure
Adjustment	DIN rail adjustment in height, pitch 25 mm
Length	32.48 in (825 mm)
Height	1.38 in (35 mm)
Width	0.28 in (7.2 mm)
Thickness	0.04 in (1 mm)

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480191688
Returnability	No
Country Of Origin	ES

### **Packing Units**

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1	
Package 1 Height	0.59 in (1.500 cm)	
Package 1 Width	1.57 in (4.000 cm)	
Package 1 Length	ength 32.48 in (82.500 cm)	
Package 1 Weight	19.44 oz (551.000 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	2	
Package 2 Height	0.79 in (2.000 cm)	
Package 2 Width	1.77 in (4.500 cm)	
Package 2 Length	32.68 in (83.000 cm)	
Package 2 Weight	2.45 lb(US) (1.111 kg)	
Unit Type Of Package 3	P12	
Number Of Units In Package 3	60	
Package 3 Height	3 Height 17.72 in (45.000 cm)	
Package 3 Width	31.50 in (80.000 cm)	
Package 3 Length	47.24 in (120.000 cm)	
Package 3 Weight	99.34 lb(US) (45.060 kg)	

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations