Product data sheet

Specifications





Earth leads section 6mm², length 220mm, eyelet hole 6,4mm. Packaging unit: 10.

NSYEL226D6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 12.98 USD

Main

Range	Spacial
Anwendung	Multi-purpose
Product Or Component Type	Earthing wire
Device Composition	1 lead
Quantity Per Set	Set of 10

Complementary

Material	PVC (polyvinyl chloride) green and yellow sheath Brass and copper alloy terminal
Fixing Mode	Nut and washer - on earth connection
Length	8.66 in (220 mm)
Nominal Cross Section	0.01 in² (6 mm²)
Diameter	0.25 in (6.4 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480181658
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1.0 cm)
Package 1 Width	0.39 in (1.0 cm)
Package 1 Length	8.66 in (22.0 cm)
Package 1 Weight	0.60 oz (17.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	0.79 in (2.0 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 2 Width	8.27 in (21.0 cm)
Package 2 Length	9.84 in (25.0 cm)
Package 2 Weight	6.28 oz (178.0 g)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	500
Package 3 Height	7.87 in (20.0 cm)
Package 3 Width	15.75 in (40.0 cm)
Package 3 Length	23.62 in (60.0 cm)
Package 3 Weight	19.62 lb(US) (8.9 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations