## Product data sheet

0

Specifications



# Earth leads section 6mm<sup>2</sup>, length 160mm, eyelet hole 8,3mm. Packaging unit: 10.

NSYEL166D8

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 1.92 USD

#### Main

Range	Spacial
Anwendung	Multi-purpose
Product Or Component Type	Earthing wire
Device Composition	1 lead
Quantity Per Set	Set of 10

#### Complementary

Material	PVC (polyvinyl chloride) green and yellow sheath Brass and copper alloy terminal
Fixing Mode	Nut and washer - on earth connection
Length	6.30 in (160 mm)
Width	0.39 in (10 mm)
Nominal Cross Section	0.01 in² (6 mm²)
Diameter	0.33 in (8.3 mm)

#### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480064401
Returnability	No
Country Of Origin	FR

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.09 in (18.01 cm)
Package 1 Width	2.76 in (7.01 cm)
Package 1 Length	0.59 in (1.5 cm)
Package 1 Weight	0.02 lb(US) (0.01 kg)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 2 Height	0.59 in (1.5 cm)
Package 2 Width	1.38 in (3.5 cm)
Package 2 Length	6.69 in (17 cm)
Package 2 Weight	4.13 oz (117 g)

#### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations