# Product data sheet

Specifications





Earth leads section 25mm², length 350mm, eyelet hole 8,3mm. Packaging unit: 10.

NSYEL3525D8

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 17.64 USD

### Main

Range	Spacial
Anwendung	Multi-purpose
Product Or Component Type	Earthing wire
Device Composition	1 lead
Quantity Per Set	Set of 10

### Complementary

Material	PVC (polyvinyl chloride) green and yellow sheath Brass and copper alloy terminal	
Fixing Mode	Nut and washer - on earth connection	
Length	13.78 in (350 mm)	
Width	0.63 in (16 mm)	
Nominal Cross Section	al Cross Section 0.04 in² (25 mm²)	
Diameter	0.33 in (8.3 mm)	

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480064418
Returnability	Yes
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.31 in (0.8 cm)
Package 1 Width	0.63 in (1.6 cm)
Package 1 Length	14.41 in (36.6 cm)
Package 1 Weight	3.67 oz (104.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Height	1.57 in (4.0 cm)
Package 2 Width	4.72 in (12.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	2.29 lb(US) (1.04 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	100
Package 3 Height	7.87 in (20.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	22.93 lb(US) (10.4 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations