Product data sheet

Specification





(!) Discontinued

EMA connectors 60x20 for symmetric C-shaped rails, C20 and C40 types; Supply: 20

NSYEMA20

! Discontinued on: May 19, 2023

! End-of-service on: Jul 6, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Category	Mounting accessory	
Product Or Component Type	Connector	
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3CM	
Application	Multi-purpose	
Nominal Dimensions Of The Housing	-	
Mounting Location	Between C20 rails	
Device Composition	1 connector	
Quantity Per Set	Set of 20	
Material	steel	

Complementary

Surface Finish	Zinc coated	
Fixing Mode	By fixing element	
Length	2.36 in (60 mm)	
Height	0.24 in (6 mm)	
Width	0.84 in (21.3 mm)	
Depth	2.36 in (60 mm)	
Thickness	0.08 in (2 mm)	

Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480181672	
Returnability	No	
Country Of Origin	FS	

Packing Units

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	2.44 in (6.2 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	4.72 in (12.0 cm)
Package 1 Weight	1.41 oz (40.0 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	2.44 in (6.2 cm)
Package 2 Width	3.35 in (8.5 cm)
Package 2 Length	4.72 in (12.0 cm)
Package 2 Weight	28.22 oz (800.0 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile