Product data sheet

Specifications





Modular spacers 79x55 for installing devices or rails. Supply: 20 units.

NSYETU79

Discontinued on: Mar 7, 2023

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Category	Mounting accessory
Product Or Component Type	Spacer
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3CM
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Mounting Location	Devices or rails
Product Destination	From the basic chassis or mounting plate
Device Composition	1 spacer
Quantity Per Set	Set of 20
Material	steel

Complementary

•	
Surface Finish	Zinc coated
Fixing Mode	By screw
Adjustment	55 mm
Height	3.11 in (79 mm)
Width	1.57 in (40 mm)
Depth	1.46 in (37 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480181771
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Height	3.54 in (9.0 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	5.12 in (13.0 cm)
Package 1 Weight	1.80 oz (51.0 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	3.54 in (9.0 cm)
Package 2 Width	3.54 in (9.0 cm)
Package 2 Length	5.12 in (13.0 cm)
Package 2 Weight	2.25 lb(US) (1.02 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile