Product data sheet





Polyester rear part of PLS box 36x36x13.5cm

NSYFPLS3636G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 73.11 USD

Main

Range	Thalassa	
Product Name	Thalassa PLS	
Device Short Name	PLS	
Enclosure Type	Multi-purpose	
Category	Insulating modular rear	
Nominal Height	14.17 in (360 mm)	
Nominal Width	14.17 in (360 mm)	
Nominal Depth	5.31 in (135 mm)	
Enclosure Mounting	Wall mounted	
Device Composition	1 rear part on enclosure	
Body Type	One piece moulded	
Type Of Front Cover	Without	

Complementary

Material	polyester reinforced with fibreglass Body Gray RAL 7035)	
Color		
Standards	NEMA 4X IEC 62208 NEMA classification 13	
Product Certifications	UL	

Environment

Electrical Insulation Class	Class II
Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK09 IEC 62262
Fire Resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature For Storage	-22158 °F (-3070 °C)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480774010

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	ES	

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	14.96 in (38.0 cm)
Package 1 Length	14.96 in (38.0 cm)
Package 1 Weight	3.31 lb(US) (1.5 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	6
Package 2 Height	17.32 in (44.0 cm)
Package 2 Width	28.74 in (73.0 cm)
Package 2 Length	14.57 in (37.0 cm)
Package 2 Weight	22.48 lb(US) (10.198 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	