

Product data sheet

Specifications



L-rail for fixing cables, PanelSeT SFN, Spacial SF, Spacial SM, steel, W800mm

NSYFCG80

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 38.70 USD

Main

Range	Spacial
Category	Cabling accessory
Product Or Component Type	Rail
Application	Multi-purpose
Nominal Dimensions Of The Housing	-

Complementary

Mounting Location	Bottom frame of enclosure
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Device Composition	fixing elements 1 rail 2 mounting support
Quantity Per Set	Set of 1
Material	steel
Surface Finish	Galvanized
Fixing Mode	Metal clamp
Adjustment	Adjustable in depth every 25 mm
Fixing Center	750 mm
Width	Nominal 31.50 in (800 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480064487
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	1.97 in (5.000 cm)
Package 1 Length	30.71 in (78.000 cm)
Package 1 Weight	4.25 lb(US) (1.926 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	144
Package 2 Height	17.72 in (45.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	637.89 lb(US) (289.344 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations