


Product data sheet

Specifications



Insulating mounting plate for enclosure H1200xW1000mm made of bakelite

NSYMB1210

Discontinued on: Apr 19, 2023

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 39.37 in (1000 mm) W: 47.24 in (1200 mm) - H: 47.24 in (1200 mm) W: 39.37 in (1000 mm)
Mounting Location	Step slide Direct fixing on backstuds
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	bakelite
Color	Black RAL 9005)

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Permanent Permissible Load	661.39 lb(US) (300 kg)
Height	45.28 in (1150 mm)
Width	37.40 in (950 mm)
Thickness	0.20 in (5 mm)
Net Weight	182.98 lb(US) (83 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480182679
Returnability	No
Country Of Origin	ES

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.20 in (0.5 cm)
Package 1 Width	37.40 in (95.0 cm)
Package 1 Length	45.87 in (116.5 cm)
Package 1 Weight	21.96 lb(US) (9.961 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations