## **Product data sheet**

Specification





# Insulating mounting plate for enclosure H600xW400mm made of bakelite

NSYMB64

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 46.40 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 23.62 in (600 mm) W: 15.75 in (400 mm)
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	bakelite
Color	Black RAL 9005)

### Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Permanent Permissible Load	132.28 lb(US) (60 kg)
Height	22.24 in (565 mm)
Width	13.78 in (350 mm)
Thickness	0.16 in (4 mm)
Net Weight	24.25 lb(US) (11 kg)

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480182754
Returnability	No
Country Of Origin	ES

## **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.4 cm)
Package 1 Width	13.78 in (35.0 cm)
Package 1 Length	22.24 in (56.5 cm)
Package 1 Weight	3.14 lb(US) (1.424 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations