Product data sheet

Specifications





Spacial SF intermediate crossbar - enclosure width: 600 mm

NSYMIC6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 195.30 USD

Main

| Range | Spacial |
|--------------------------------------|---------------------------------------|
| Product Or Component Type | Intermediate crossbar |
| Application | Compartmentalised application |
| Nominal Dimensions Of The Housing | - W: 23.62 in (600 mm) |
| Mounting Location | Front of enclosure |
| Range Compatibility | Spacial SF compartimentalised version |
| Device Composition | Fixing elements 2 x crossbar |

Complementary

| Material | steel |
|----------------|--|
| Color | Gray RAL 7035) |
| Surface Finish | Epoxy-polyester powder |
| Fixing Mode | By fixing element - on structure |
| Adjustment | Adjustable in height every 25 mm between partial doors |
| Width | Nominal 23.62 in (600 mm) Real 22.05 in (560 mm) |
| Depth | 2.56 in (65 mm) |

Ordering and shipping details

| Category | US10ES180036 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480065576 |
| Returnability | No |
| Country Of Origin | ES |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.95 in (7.5 cm) |
| Package 1 Width | 4.02 in (10.2 cm) |
| Package 1 Length | 24.02 in (61.0 cm) |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Package 1 Weight | 4.74 lb(US) (2.152 kg) |
|------------------------------|--------------------------|
| Unit Type Of Package 2 | РАМ |
| Number Of Units In Package 2 | 100 |
| Package 2 Height | 17.72 in (45.0 cm) |
| Package 2 Width | 39.37 in (100.0 cm) |
| Package 2 Length | 47.24 in (120.0 cm) |
| Package 2 Weight | 540.13 lb(US) (245.0 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |