



Plain mounting plate H200xW400mm made of galvanised sheet steel

NSYMM24SB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 23.34 USD

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	-	
Mounting Location	Bottom of enclosure	
Mounting Plate Description	Plain	
Range Compatibility	Spacial Spacial SBM	
Device Composition	omposition 1 mounting plate	
Material	galvanised steel	
Surface Finish	Metallic	

Complementary

Fixing Mode	By 2 screws Ø5 mm self-tapping screws - bottom of enclosure	
Permanent Permissible Load	8.82 lb(US) (4 kg) back of the enclosure	
Height	Nominal 6.89 in (175 mm)	
Width	Nominal 15.16 in (385 mm) Fixing centers 14.33 in (364 mm)	
Surface And Useful Surface	Nominal 124.00 in² (80000 mm²)	
Thickness	0.08 in (2 mm)	
Net Weight	2.28 lb(US) (1.032 kg)	

Ordering and shipping details

Category	US10ES180033
Discount Schedule	0ES1
Gtin	3606480520563
Returnability	No
Country Of Origin	IN

Packing Units

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	0.12 in (0.3 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	15.35 in (39.0 cm)
Package 1 Weight	2.28 lb(US) (1.032 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	500
Package 2 Height	17.72 in (45.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1166.25 lb(US) (529.0 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations