

Product data sheet

Specifications



Spacial SF/SM mounting plate - 1200x1200 mm

NSYMP1212

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 193.03 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 47.24 in (1200 mm) W: 47.24 in (1200 mm)
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Device Composition	1 mounting plate 2 sliding shoes
Quantity Per Set	Set of 1
Material	galvanised steel

Complementary

Fixing Mode	By fixing brackets
Maximum Load	300 kg/m²
Permanent Permissible Load	1102.31 lb(US) (500 kg) intermediate position 1322.77 lb(US) (600 kg) back of the enclosure
Height	Fixing centers 41.34 in (1050 mm) Nominal 47.24 in (1200 mm) Real 43.19 in (1097 mm)
Width	Fixing centers 41.34 in (1050 mm) Nominal 47.24 in (1200 mm) Real 43.15 in (1096 mm)
Depth	1.06 in (27 mm)

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485130675
Returnability	No
Country Of Origin	ES

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	43.70 in (111.0 cm)
Package 1 Width	43.70 in (111.0 cm)
Package 1 Length	1.57 in (4.0 cm)
Package 1 Weight	68.34 lb(US) (31.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations