Product data sheet

Specifications





Plain mounting plate H300xW200mm made of galvanised sheet steel

NSYMM32

Product availability: Stock - Normally stocked in distribution facility

Price*: 7.70 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 11.81 in (300 mm) W: 7.87 in (200 mm)
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	galvanised steel

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Permanent Permissible Load	132.28 lb(US) (60 kg)
Height	9.84 in (250 mm)
Width	5.91 in (150 mm)
Thickness	0.07 in (1.8 mm)
Net Weight	1.15 lb(US) (0.52 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480183294
Returnability	Yes
Country Of Origin	ES

Packing Units

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	0.12 in (0.3 cm)
Package 1 Width	5.91 in (15.0 cm)
Package 1 Length	9.84 in (25.0 cm)
Package 1 Weight	18.77 oz (532.0 g)
Unit Type Of Package 2	P12
Number Of Units In Package 2	300
Package 2 Height	16.14 in (41.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	394.19 lb(US) (178.8 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations