



# Plain mounting plate H300xW600mm made of galvanised sheet steel

NSYMM36SB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 56.68 USD

### Main

| Range                               | Spacial                      |  |
|-------------------------------------|------------------------------|--|
| Accessory / Separate Part Category  | Mounting accessory           |  |
| Product Or Component Type           | Mounting plate               |  |
| Device Application                  | Multi-purpose                |  |
| <b>Enclosure Nominal Dimensions</b> | -                            |  |
| Mounting Location                   | Bottom of enclosure          |  |
| Mounting Plate Description          | Plain                        |  |
| Range Compatibility                 | Spacial Spacial SBM          |  |
| Device Composition                  | composition 1 mounting plate |  |
| Material                            | galvanised steel             |  |
| Surface Finish                      | Metallic                     |  |

## Complementary

| Fixing Mode                | By 2 screws Ø5 mm self-tapping screws - bottom of enclosure |
|----------------------------|---|
| Permanent Permissible Load | 19.84 lb(US) (9 kg) back of the enclosure                   |
| Height                     | Nominal 10.83 in (275 mm)                                   |
| Width                      | Nominal 23.03 in (585 mm) Fixing centers 22.20 in (564 mm)  |
| Surface And Useful Surface | Nominal 279.00 in <sup>2</sup> (180000 mm <sup>2</sup> )    |
| Thickness                  | 0.08 in (2 mm)  |
| Net Weight                 | 5.44 lb(US) (2.466 kg)                                      |

## Ordering and shipping details

| Category          | US10ES180033  |
|-------------------|---------------|
| Discount Schedule | 0ES1          |
| Gtin              | 3606480520631 |
| Returnability     | No            |
| Country Of Origin | IN            |

## **Packing Units**

| Unit Type Of Package 1 | PCE |
|------------------------|-----|
|------------------------|-----|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Number Of Units In Package 1 | 1                         |
|------------------------------|---------------------------|
| Package 1 Height             | 0.12 in (0.3 cm)          |
| Package 1 Width              | 11.02 in (28.0 cm)        |
| Package 1 Length             | 23.23 in (59.0 cm)        |
| Package 1 Weight             | 5.44 lb(US) (2.466 kg)    |
| Unit Type Of Package 2       | PAM                       |
| Number Of Units In Package 2 | 200                       |
| Package 2 Height             | 17.72 in (45.0 cm)        |
| Package 2 Width              | 39.37 in (100.0 cm)       |
| Package 2 Length             | 47.24 in (120.0 cm)       |
| Package 2 Weight             | 1115.54 lb(US) (506.0 kg) |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>Ø</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>Ø</b> | Toxic Heavy Metal Free     |     |
| <b>②</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration           |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |