Product data sheet

Specifications





Insulating polyester mounting plate for PLS box 54x72cm

NSYPMA5472G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 122.73 USD

Main

Range	Thalassa
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 21.26 in (540 mm) W: 28.35 in (720 mm)
Mounting Location	Back inserts
Mounting Plate Description	Insulating
Range Compatibility	Thalassa Thalassa PLS
Device Composition	1 mounting plate
Material	polyester
Color	Gray RAL 7035)

Complementary

Fixing Mode	By screws M6 - on back inserts
Permanent Permissible Load	330.69 lb(US) (150 kg)
Height	Real 19.69 in (500 mm)
Width	Real 26.77 in (680 mm)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606485405414
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.20 in (0.500 cm)
Package 1 Width	19.69 in (50.000 cm)
Package 1 Length	26.97 in (68.500 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Weight	4.94 lb(US) (2.240 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	40
Package 2 Height	17.72 in (45.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	223.99 lb(US) (101.600 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations