Product data sheet

Specification





Monobloc perforated plates H300xW250mm with universal perforations 11x26mm

NSYMR3025

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 42.60 USD

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 11.81 in (300 mm) W: 9.84 in (250 mm)	
Mounting Location	Direct fixing on backstuds Step slide	
Mounting Plate Description	Telequick perforated	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	ty Per Set Set of 1	
Material	steel	
Surface Finish	Zinc coated	

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element	
Height	9.96 in (253 mm)	
Width	8.98 in (228 mm)	
Depth	0.59 in (15 mm)	
Thickness	0.08 in (2 mm)	
Net Weight	1.02 lb(US) (0.463 kg)	
Number Of Slots	128	
Variant Particularity	Installation in rear of enclosure	
Cut-Out Dimensions	11 x 26 mm	

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480183607
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin FR

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	9.06 in (23.0 cm)
Package 1 Length	10.04 in (25.5 cm)
Package 1 Weight	16.01 oz (454.0 g)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	368
Package 2 Height	19.69 in (50.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	396.83 lb(US) (180.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations