



reversible internal door polyester 2 locks grid pattern forPLM108

NSYPAP108G

Product availability: Stock - Normally stocked in distribution facility

Price*: 190.10 USD

Main

Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front side
Range Compatibility	Thalassa Thalassa PLM
Device Composition	1 door 1 handle 4 fixing brackets

Complementary

Material	polyester charged with fibreglass
Color	Gray RAL 7035)
Lock Type	Lock 5 mm double bar
Number Of Locks	2
Door Type	Internal plain
Door Opening Side	Reversible 110 °)
Height	Grid pattern: 33.46 in (850 mm)
Width	Grid pattern: 25.59 in (650 mm)
Depth	Available depth between enclosure door 1.46 in (37 mm) Available depth between rear 10.59 in (269 mm)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480774171
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	31.10 in (79.000 cm)
Package 1 Length	38.98 in (99.000 cm)
Package 1 Weight	6.04 lb(US) (2.741 kg)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	11.42 in (29.000 cm)
Package 2 Width	35.43 in (90.000 cm)
Package 2 Length	39.37 in (100.000 cm)
Package 2 Weight	30.91 lb(US) (14.021 kg)
Unit Type Of Package 3	PAM
Number Of Units In Package 3	30
Package 3 Height	53.15 in (135.000 cm)
Package 3 Width	39.37 in (100.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	214.13 lb(US) (97.126 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations