# **Product data sheet**

Specifications





# Spacial SF/SM canopy - 1200x300 mm

NSYSC1230

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 439.81 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Canopy
Application	Multi-purpose
Range Compatibility	Spacial Spacial SM
For Enclosure Nominal Dimensions	-
Mounting Location	On top of enclosure
Device Composition	1 canopy fixing elements drilling template

# Complementary

Quantity Per Set	Set of 1
Material	galvanised steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws - roof drilled holes
Height	3.35 in (85 mm)
Width	Nominal: 47.24 in (1200 mm) Real: 47.52 in (1207 mm)
Depth	Nominal 11.81 in (300 mm) Real 12.80 in (325 mm)

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485131122
Returnability	No
Country Of Origin	ES

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	13.19 in (33.5 cm)
Package 1 Length	48.03 in (122.0 cm)
Package 1 Weight	15.63 lb(US) (7.09 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations