Product data sheet

Specifications





internal door for PLA enclosure H500xW750 mm

NSYPAPLA57G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 314.29 USD

Main

| Range | Thalassa |
|---------------------------------------|---|
| Accessory / Separate Part Category | Enclosure accessory |
| Product Or Component Type | Door |
| Application | Multi-purpose |
| For Enclosure Nominal Dimensions | - |
| Mounting Location | Front side |
| Range Compatibility | Thalassa Thalassa PLA |
| Device Composition | 1 door fixing elements M8 brass inserts |

Complementary

| Material | aluminium |
|-------------------|--|
| Color | Gray RAL 7035) |
| Lock Type | Lock 5 mm double bar |
| Number Of Locks | 2 |
| Door Type | Internal plain |
| Door Opening Side | Left 110 °) |
| Height | 15.67 in (398 mm) |
| Width | 25.51 in (648 mm) |
| Depth | Available depth between enclosure door 1.18 in (30 mm) |

Ordering and shipping details

| Category | US10ES180034 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480774300 |
| Returnability | No |
| Country Of Origin | FS |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Height | 1.57 in (4.0 cm) |
|------------------|----------------------|
| Package 1 Width | 25.98 in (66.0 cm) |
| Package 1 Length | 16.14 in (41.0 cm) |
| Package 1 Weight | 6.39 lb(US) (2.9 kg) |



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |