# Product data sheet

Specifications





# Insulating polyester mounting plate for PLS box 36x54cm

NSYPMA3654G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 34.07 USD

#### Main

| Range                                 | Thalassa                                    |  |
|---------------------------------------|---|--|
| Accessory / Separate Part<br>Category | Mounting accessory                          |  |
| Product Or Component Type             | Mounting plate                              |  |
| Device Application                    | Multi-purpose                               |  |
| Enclosure Nominal Dimensions          | - H: 14.17 in (360 mm) W: 21.26 in (540 mm) |  |
| Mounting Location                     | Back inserts                                |  |
| Mounting Plate Description            | Insulating                                  |  |
| Range Compatibility                   | Thalassa Thalassa PLS                       |  |
| Device Composition                    | 1 mounting plate                            |  |
| Material                              | polyester                                   |  |
| Color                                 | Gray RAL 7035)                              |  |

### Complementary

| Fixing Mode                | By screws M6 - on back inserts |  |
|----------------------------|--------------------------------|--|
| Permanent Permissible Load | 330.69 lb(US) (150 kg)         |  |
| Height                     | Real 12.60 in (320 mm)         |  |
| Width                      | Real 19.69 in (500 mm)         |  |

# Ordering and shipping details

| Category          | US10ES180034  |
|-------------------|---------------|
| Discount Schedule | 0ES1          |
| Gtin              | 3606485405384 |
| Returnability     | No            |
| Country Of Origin | ES            |

# **Packing Units**

| Unit Type Of Package 1       | PCE                |  |
|------------------------------|--------------------|--|
| Number Of Units In Package 1 | 1                  |  |
| Package 1 Height             | 0.20 in (0.5 cm)   |  |
| Package 1 Width              | 19.69 in (50.0 cm) |  |
| Package 1 Length             | 12.60 in (32.0 cm) |  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight

2.59 lb(US) (1.174 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

| <b>Ø</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>Ø</b> | Toxic Heavy Metal Free     |     |
| <b>②</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration           |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |