



One symmetric mounting rail 35x7.5 L2000mm type B, Order by Multiples of 10 units

NSYSDR200B

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 7.36 USD

Main

Anwendung	Multi-purpose	
Range	Spacial	
Product Or Component Type	Rail	
Accessory / Separate Part Category	Mounting accessory	
Type Of Rail	Symmetrical DIN	
Enclosure Nominal Dimensions	-	
Range Compatibility	Spacial Thalassa	
Device Composition	mposition 1 rail	
Quantity Per Set	Set of 10	

Complementary

Material	galvanised steel
Surface Finish	Not perforated
Fixing Mode	By fixing element - structure of enclosure
Adjustment	Continuous adjustment Pitch 25 mm
Length	78.74 in (2000 mm)
Height	Nominal: 0.28 in (7.2 mm)
Width	Nominal: 1.38 in (35 mm)
Thickness	0.04 in (1 mm)

Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480184321	
Returnability	No	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	0.28 in (0.700 cm)	
Package 1 Width	1.46 in (3.700 cm)	
Package 1 Length	78.74 in (200.000 cm)	
Package 1 Weight	23.28 oz (660.000 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	10	
Package 2 Height	1.57 in (4.000 cm)	
Package 2 Width	1.77 in (4.500 cm)	
Package 2 Length	78.94 in (200.500 cm)	
Package 2 Weight	14.99 lb(US) (6.800 kg)	
Unit Type Of Package 3	P2M	
Number Of Units In Package 3	600	
Package 3 Height	17.72 in (45.000 cm)	
Package 3 Width	78.74 in (200.000 cm)	
Package 3 Length	47.24 in (120.000 cm)	
Package 3 Weight	906.10 lb(US) (411.000 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations