


# Product data sheet

Specifications



## Spacial SF bottom and top frame - 1200x500 mm

NSYSFC125

Product availability: Stock - Normally stocked in distribution facility

Price\*: 654.62 USD

### Main

Range	PanelSeT
Accessory / Separate Part Category	Enclosure accessory
Application	Multi-purpose
Product Or Component Type	Framework kit
For Enclosure Nominal Dimensions	-
Mounting Location	Top of vertical uprights Bottom of vertical uprights
Range Compatibility	PanelSeT rear panel PanelSeT side panel PanelSeT vertical upright
Device Composition	1 bottom frame 1 roof 1 top frame
Quantity Per Set	Set of 1

### Complementary

Material	steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws - each corner of enclosure
Width	47.24 in (1200 mm)
Depth	19.69 in (500 mm)

### Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485119076
Returnability	No
Country Of Origin	ES

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	23.23 in (59.0 cm)
Package 1 Length	48.43 in (123.0 cm)
Package 1 Weight	72.97 lb(US) (33.1 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	8
Package 2 Height	47.24 in (120 cm)
Package 2 Width	31.50 in (80 cm)
Package 2 Length	57.09 in (145 cm)
Package 2 Weight	573.20 lb(US) (260 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.