# Product data sheet

Specifications





One symmetric mounting rail perforated 35x7.2 mm L2000 mm type B, Order by Multiples of 10 units

NSYSDR200BD

Product availability: Stock - Normally stocked in distribution facility

Price\*: 7.52 USD

#### Main

Anwendung	Multi-purpose	
Range	Spacial	
Product Or Component Type	Rail	
Device Short Name	TR	
Accessory / Separate Part Category	Mounting accessory	
Type Of Rail	Symmetrical DIN	
Enclosure Nominal Dimensions	-	
Range Compatibility	Spacial Thalassa	
Device Composition	1 rail	
Quantity Per Set	Set of 10	

### Complementary

Material	galvanised steel
Surface Finish	Perforated
Fixing Mode	By fixing element - structure of enclosure
Adjustment	Pitch 25 mm Continuous adjustment
Length	78.74 in (2000 mm)
Height	Nominal: 0.28 in (7.2 mm)
Width	Nominal: 1.38 in (35 mm)
Thickness	0.04 in (1 mm)

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480184338
Returnability	Yes
Country Of Origin	IT

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Packing Units**

_		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	0.59 in (1.500 cm)	
Package 1 Width	1.18 in (3.000 cm)	
Package 1 Length	78.74 in (200.000 cm)	
ackage 1 Weight 21.02 oz (596.000 g)		
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	10	
Package 2 Height	1.57 in (4.000 cm)	
Package 2 Width	1.57 in (4.000 cm)	
Package 2 Length	78.74 in (200.000 cm)	
Package 2 Weight	14.74 lb(US) (6.684 kg)	
Unit Type Of Package 3	P2M	
Number Of Units In Package 3	400	
Package 3 Height	35.43 in (90.000 cm)	
Package 3 Width	78.74 in (200.000 cm)	
Package 3 Length	47.24 in (120.000 cm)	
Package 3 Weight	558.65 lb(US) (253.400 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations