# Product data sheet

Specifications





# One symmetric mounting rail 35x15 L800mm type A Supply: 20

NSYSDR80A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 30.87 USD

#### Main

Anwendung	Multi-purpose	
Range	Spacial	
Product Or Component Type	Rail	
Accessory / Separate Part Category	Mounting accessory	
Type Of Rail	Symmetrical DIN	
<b>Enclosure Nominal Dimensions</b>	-	
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX Spacial Spacial SD	
Device Composition	fixing elements 1 rail	
Quantity Per Set	Set of 20	

### Complementary

Material	zinc coated steel
Surface Finish	Zinc coated
Fixing Mode	By fixing element - structure of enclosure
Adjustment	Pitch 25 mm Continuous adjustment
Length	Nominal 31.50 in (800 mm) Real 29.53 in (750 mm)
Height	Nominal: 0.59 in (15 mm)
Width	Nominal: 1.38 in (35 mm)
Thickness	0.06 in (1.5 mm)

#### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480184390
Returnability	No
Country Of Origin	FR

# **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	1.38 in (3.5 cm)
Package 1 Length	29.33 in (74.5 cm)
Package 1 Weight	15.03 oz (426.0 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations