

# Product data sheet

## Characteristics

# NSYSFX181240

SFX 304L stainless suitable enclosure,  
H1800xW1200xD400mm, Scotch Brite® finish.

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 7,155.47 USD



### Main

Range	Spacial
Product name	Spacial SFX
Enclosure type	Multi-purpose
Category	Suitable enclosure
Nominal height	70.87 in (1800 mm)
Nominal width	47.24 in (1200 mm)
Nominal depth	15.75 in (400 mm)
Product installation	Floor-standing
Device composition	1 cable gland plate 1 structure 4 mounting plate bracket 1 locking system with handle ( door ) 2 door with reinforcement frame

### Complementary

Body type	Rear panel integrated Single piece structure folded and welded
Door type	Plain
Number of doors	Front face: 2 door(s)
Door opening side	120 °, reversible
Lock type	3 points lock, handle with 5 mm double-bar insert
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front Side
Removable parts	Door fixing: by hinges Mounting plate bracket fixing: by screws Cable gland plate fixing: by clips

Material	Hinge: stainless steel Structure and door : stainless steel 304L Handle : zamak
Surface finish	Enclosure : Scotch-Brite® brushed Handle : painted
Product weight	264.55 lb(US) (120 kg)

## Environment

Standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Corrosive Specific hygiene

## Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	003606480155628
Nbr. of units in pkg.	1
Package weight(Lbs)	264
Returnability	N
Country of origin	BG

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------