

# Product data sheet

## Characteristics

# NSYSM1210302DP

Spacial SM compact enclosure with mounting plate - 1200x1000x300 mm

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,047.21 USD



### Main

Range	Spacial
Product name	Spacial SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 blocking system left door 1 body 1 cable gland plate 1 mounting plate 1 locking system with handle door 4 mounting plate bracket 2 door
Removable parts	Door fixed by screws hinge Mounting plate bracket fixed by screws Mounting plate fixed by screws mounting plate bracket
Enclosure nominal height	47.24 in (1200 mm)
Enclosure nominal width	39.37 in (1000 mm)
Enclosure nominal depth	11.81 in (300 mm)

### Complementary

Number of doors	2 on front
Door opening side	Left 120 ° Right 120 °
Door type	Plain
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting plate description	Plain
Type of gland plate	Standard

Cable entry	1 entry
Material	Galvanised steel mounting plate Sheet steel body Sheet steel door Zamak hinge
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey RAL 7035 Handle: black RAL 9005
Accessibility for operation	Front

## Environment

Standards	IEC 62208
Product certifications	BV DNV UL
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

## Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	003606485120027
Nbr. of units in pkg.	1
Package weight(Lbs)	184.80000000000001
Returnability	N
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------