Product data sheet

Specifications





Spacial SF double plain doors - 1800x800 mm

NSYSFD1882D

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 449.22 USD

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Spacial Spacial SF
Device Composition	1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 2 door 1 blocking system 2 reinforcement frame 8 hinges
Quantity Per Set	Set of 1

Complementary

Material	sheet steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	External plain
Door Opening Side	Reversible 120 °)
Maximum Load	60 kg/m²
Height	Nominal: 70.87 in (1800 mm)
Width	Nominal: 31.50 in (800 mm)

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606480067594
Returnability	No
Country Of Origin	ES

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	17.32 in (44.0 cm)
Package 1 Length	74.41 in (189.0 cm)
Package 1 Weight	70.55 lb(US) (32.0 kg)
Unit Type Of Package 2	P2M
Number Of Units In Package 2	10
Package 2 Height	38.19 in (97.0 cm)
Package 2 Width	78.74 in (200.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	776.03 lb(US) (352.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations