## Product data sheet

Specifications





# Spacial SF transparent door - 1800x800 mm

NSYSFD188T

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 840.14 USD

#### Main

Range	Spacial	
Accessory / Separate Part Category	Enclosure accessory	
Product Or Component Type	Door	
Application	Multi-purpose	
For Enclosure Nominal Dimensions	-	
Mounting Location	Side Front	
Range Compatibility	Spacial Spacial SF	
Device Composition	1 door 1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 4 hinges 4 locking bar catches	
Quantity Per Set	Set of 1	

#### Complementary

Material	Door Securit glass Door sheet steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	External transparent
Door Opening Side	Reversible 120 °)
Height	Nominal 70.87 in (1800 mm)
Width	Nominal 31.50 in (800 mm)

### Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485119663
Returnability	No
Country Of Origin	ES

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6.0 cm)
Package 1 Width	30.91 in (78.5 cm)
Package 1 Length	74.41 in (189.0 cm)
Package 1 Weight	44.97 lb(US) (20.4 kg)
Unit Type Of Package 2	P2M
Number Of Units In Package 2	10
Package 2 Height	30.31 in (77.0 cm)
Package 2 Width	78.74 in (200.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	520.29 lb(US) (236.0 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations