

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,062.05 USD



Main

| | |
|-----------------------------|--|
| Range | Spacial |
| Product name | Spacial SM |
| Product or component type | Compact enclosure |
| Application | Multi-purpose |
| Installation accessory type | Floor-standing |
| Device composition | 1 body 1 cable gland plate 1 door 1 locking system with handle door 4 mounting plate bracket |
| Removable parts | Door fixed by screws hinge Mounting plate bracket fixed by screws |
| Enclosure nominal height | 55.12 in (1400 mm) |
| Enclosure nominal width | 31.5 in (800 mm) |
| Enclosure nominal depth | 11.81 in (300 mm) |

Complementary

| | |
|----------------------------|--|
| Number of doors | 1 on front |
| Door opening side | Reversible 120 ° |
| Door type | Plain |
| Lock type | 4 points lock, handle with 5 mm double bar insert |
| Body type | Single piece body with welded rear panel Front part forming a rigid frame with welded corners |
| Mounting plate description | Without mounting plate |
| Type of gland plate | Standard |
| Cable entry | 1 entry |
| Material | Sheet steel body Sheet steel door |

| | |
|-----------------------------|--|
| | Zamak hinge |
| Surface finish | Epoxy-polyester powder |
| Colour | Enclosure: grey RAL 7035 Handle: black RAL 9005 |
| Accessibility for operation | Front |

Environment

| | |
|-------------------------|------------------------------|
| Standards | IEC 62208 |
| Product certifications | BV DNV UL |
| IP degree of protection | IP55 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

Ordering and shipping details

| | |
|-----------------------|---------------------------------------|
| Category | 80035 - ENCLOSURE SYSTEMS FLOOR MOUNT |
| Discount Schedule | ES1 |
| GTIN | 003606485120515 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 132 |
| Returnability | N |
| Country of origin | ES |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |
| California proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|