



Cable ducting support to be used with 22mm-diameter products

NSYSPCP

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1.98 USD

Main

| Accessory / Separate Part Category | Cable management accessory |
|---------------------------------------|--|
| Product Or Component Type | Support |
| Product Destination | Cable duct |
| Range Compatibility | Thalassa Thalassa PLA Thalassa Thalassa PLS Thalassa Thalassa PLM Spacial Spacial SBM Spacial Spacial S3D Spacial Spacial S3CM Spacial Spacial CRN |
| Anwendung | Multi-purpose |
| Mounting Support | Door |
| Device Composition | 1 support |
| Quantity Per Set | Set of 10 |
| | |

Complementary

| Material | Galvanised steel |
|-------------|-------------------------------------|
| Fixing Mode | By screws on 22 mm equipment |
| Height | 3.94 in (100 mm) |
| Width | 1.18 in (30 mm) |
| Depth | 0.45 in (11.5 mm) |
| Diameter | 0.89 in (22.5 mm) 0.00 in (0 mm) |

Ordering and shipping details

| Category | US10ES180036 | |
|-------------------|---------------|--|
| Discount Schedule | 0ES1 | |
| Gtin | 3606480184482 | |
| Returnability | No | |
| Country Of Origin | FR | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.18 in (3.0 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Width | 1.38 in (3.5 cm) |
|------------------------------|-------------------------|
| Package 1 Length | 4.33 in (11.0 cm) |
| Package 1 Weight | 1.06 oz (30.0 g) |
| Unit Type Of Package 2 | BAG |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 1.18 in (3.0 cm) |
| Package 2 Width | 1.57 in (4.0 cm) |
| Package 2 Length | 4.33 in (11.0 cm) |
| Package 2 Weight | 10.62 oz (301.0 g) |
| Unit Type Of Package 3 | S01 |
| Number Of Units In Package 3 | 160 |
| Package 3 Height | 5.91 in (15.0 cm) |
| Package 3 Width | 5.91 in (15.0 cm) |
| Package 3 Length | 15.75 in (40.0 cm) |
| Package 3 Weight | 10.88 lb(US) (4.933 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ② | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| 9 | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |