# Product data sheet





## 4 fixed screw jacks - 42mm maximum load: 100kg per jack

NSYSPSJ

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 152.76 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Installation accessory
Product Or Component Type	Levelling feet
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Range Compatibility	Spacial Spacial SF suitable enclosure Spacial Spacial SM compact enclosure Spacial Spacial SD control desk Spacial Spacial SFX suitable enclosure Spacial Spacial SMX compact enclosure Spacial Spacial SDX control desk
Device Composition	4 feets
Quantity Per Set	Set of 1

#### Complementary

Material	Steel
Fixing Mode	By screws - structure of enclosure
Adjustment	Adjustable in height every 42 mm
Permanent Permissible Load	220.46 lb(US) (100 kg)
Height	1.65 in (42 mm)

#### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485132617
Returnability	No
Country Of Origin	FR

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.12 in (13.0 cm)
Package 1 Width	4.33 in (11.0 cm)
Package 1 Length	1.97 in (5.0 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Weight

4.85 lb(US) (2.2 kg)

### **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations