

Product data sheet

Specifications



Polyester canopy for PLA enclosure W1250xD320 mm



NSYTJPLA123G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 80.35 USD

Main

Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Canopy
Application	Multi-purpose
Range Compatibility	Thalassa Thalassa PLA
For Enclosure Nominal Dimensions	-
Mounting Location	On top of enclosure
Device Composition	1 canopy fixing elements drilling template

Complementary

Material	polyester charged with fibreglass
Color	Gray RAL 7035)
Fixing Mode	By fixing element
Height	1.50 in (38 mm)
Width	49.21 in (1250 mm)
Depth	12.60 in (320 mm)

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480777370
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	13.78 in (35.000 cm)
Package 1 Length	50.79 in (129.000 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	9.81 lb(US) (4.452 kg)
Unit Type Of Package 2	P2M
Number Of Units In Package 2	20
Package 2 Height	35.43 in (90.000 cm)
Package 2 Width	78.74 in (200.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	224.12 lb(US) (101.660 kg)

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations