# Product data sheet

Specifications





# Standard for Spacial S3D encl. RAL7035, L245xW130

NSYTLCFL

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 13.00 USD

## Main

Range	Spacial
Product Or Component Type	Cable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Nominal Width Of The Housing	11.81 in (300 mm)
Nominal Depth Of The Housing	7.87 in (200 mm)
Range Compatibility	Spacial Spacial SF Spacial Spacial S3D
Mounting Location	Enclosure bottom
Cable Gland Type	With FL cut-out
Device Composition	fixing elements 1 plate 1 separate gasket
Quantity Per Set	Set of 1
Material	Plate steel Seal polyethylene (PE) foam

## Complementary

Color	Plate Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Height	9.65 in (245 mm)
Width	9.65 in (245 mm) Real 15.75 in (400 mm)
Depth	5.12 in (130 mm) Real 7.87 in (200 mm)
Net Weight	1212.54 lb(US) (550 kg)
Thickness	0.06 in (1.5 mm)
Number Of Cut-Out	1 cut-out
Accessory / Separate Part Destination	For FL21 membranes
Cut-Out Dimensions	194 x 62.5 mm

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	3606480168451
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.43 in (1.1 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	10.08 in (25.6 cm)
Package 1 Weight	8.47 oz (240.0 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations