Product data sheet

Specifications





Spacial WM enclosure canopy W600xD400 Colour RAL7035.. Fixings supplied.

NSYTJ6040

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 111.40 USD

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Canopy
Application	Multi-purpose
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3D
For Enclosure Nominal Dimensions	-
Mounting Location	On top of enclosure
Device Composition	canopy fixing elements instruction sheet

Complementary

Material	galvanised steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By 4 screws M6
Height	1.65 in (42 mm)
Width	Nominal: 23.62 in (600 mm) Real: 23.98 in (609 mm)
Depth	Nominal 15.75 in (400 mm) Real 16.32 in (414.5 mm)
Net Weight	9.04 lb(US) (4.1 kg)
Mounting Diameter	0.31 in (8 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480198717
Returnability	No
Country Of Origin	ES

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.77 in (4.500 cm)
Package 1 Width	16.73 in (42.500 cm)
Package 1 Length	24.21 in (61.500 cm)
Package 1 Weight	8.88 lb(US) (4.029 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	20
Package 2 Height	17.72 in (45.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	204.10 lb(US) (92.580 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations