Product data sheet







NSYTLD

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 24.06 USD

Main

Range	Spacial
Product Or Component Type	Cable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRNG
Mounting Location	Enclosure bottom
Cable Gland Type	Standard
Device Composition	fixing elements 1 plate 1 separate gasket
Quantity Per Set	Set of 1
Material	Plate steel Seal polyethylene (PE) foam

Complementary

Color	Plate Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Number Of Cut-Out	33 markings 0.98 in (25 mm)
Height	13.58 in (345 mm) 0.39 in (10 mm)
Width	13.58 in (345 mm) Real 13.78 in (350 mm)
Depth	5.12 in (130 mm)
Net Weight	1.72 lb(US) (0.78 kg)
Thickness	0.06 in (1.5 mm) 0.07 in (1.8 mm) 0.08 in (2.0 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480168420
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.20 in (0.5 cm)
Package 1 Width	5.91 in (15 cm)
Package 1 Length	13.78 in (35 cm)
Package 1 Weight	21.45 oz (608 g)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	600
Package 2 Height	27.17 in (69 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	897.28 lb(US) (407 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations