

# Product data sheet

Specifications



Plug-in bridge, Linergy TR, 10 points, for 4mm<sup>2</sup> terminal blocks, blue, 10 way, set of 10

NSYTRAL410BL

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 4.40 USD

## Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Plug-in bridge
Device Short Name	TRA
Accessory / Separate Part Category	Connection accessory
Product Compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number Of Ways	10 ways

## Complementary

Cable Cross Section	0.01 in² (4 mm²)
Number Of Connections	4 3 2
Number Of Measurement Input	1 6 4 3 2
Quantity Per Set	Set of 10
Net Weight	0.36 oz (10.1 g)
Color	Blue

## Ordering and shipping details

Category	US10CP521715
Discount Schedule	0CP5
Gtin	3606480534188
Returnability	Yes
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	0.39 in (1.0 cm)
Package 1 Width	3.15 in (8.0 cm)
Package 1 Length	6.10 in (15.5 cm)
Package 1 Weight	0.32 oz (9.0 g)
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	0.39 in (1.0 cm)
Package 2 Width	3.15 in (8.0 cm)
Package 2 Length	6.10 in (15.5 cm)
Package 2 Weight	3.49 oz (99.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	400
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	9.17 lb(US) (4.159 kg)

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations