

Product data sheet

Specifications



Cable passages IP65, round, M63, w/o connectors, 13 entries.

NSYTSAM6313SE

Discontinued on: Jul 3, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Discontinued

Main

Range	Spacial
Product Or Component Type	Quick entrance plate
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure Spacial Spacial S3CM control enclosure Spacial Spacial SBM industrial box Thalassa Thalassa PLA suitable enclosure Thalassa Thalassa PHD suitable enclosure Thalassa Thalassa PLM compact enclosure Thalassa Thalassa PLS insulating modular box Spacial Spacial S3HD compact enclosure
Device Composition	1 circular plate
Quantity Per Set	Set of 10

Complementary

Mounting Support	Cable gland plate Body of enclosure
Material	polyamide
Fixing Mode	Clipped By screws
Total Cable Entry Number	13
Cable Entry Number	1 x 0.24...0.39 in (6...10 mm) 6 x 0.14...0.26 in (3.6...6.5 mm) 6 x 0.12...0.22 in (3...5.5 mm)
Height	Real 1.34 in (34 mm)
Cable Outer Diameter	2.80 in (71 mm) 2.50 in (63.5 mm)
Net Weight	1.54 lb(US) (0.7 kg)

Environment

Ip Degree Of Protection	IP65
-------------------------	------

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	3606480168178
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.81 in (30.0 cm)
Package 1 Width	5.91 in (15.0 cm)
Package 1 Length	3.15 in (8.0 cm)
Package 1 Weight	24.69 oz (700.0 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)


[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations