# **Product data sheet**

Specifications





Telescopic rails, PanelSeT SFN, Spacial SF, Spacial SM, for electrical enclosure W600/800 D500mm, steel

NSYTTG50

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 429.31 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Installation accessory
Product Or Component Type	Telescopic rail
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
<b>Mounting Support</b>	Direct to the structure 40 mm cross rails
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
<b>Device Composition</b>	fixing elements 2 telescopic rails
Quantity Per Set	Set of 1

## Complementary

Material	steel
Surface Finish	Zinc coated
Permanent Permissible Load	55.12 lb(US) (25 kg) evenly distributed
Depth	Nominal 19 69 in (500 mm)

## Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480068171	
Returnability	No	
Country Of Origin	FR	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	6.50 in (16.5 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Length	20.87 in (53.0 cm)
Package 1 Weight	2.77 lb(US) (1.256 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	15
Package 2 Height	7.87 in (20.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	41.54 lb(US) (18.84 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations