Product data sheet

Specifications





Set of 2 heavy duty vertical rails for fixing of chassis and cross rails-1400 mm

NSYTVR14

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 200.91 USD

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Technical upright	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 55.12 in (1400 mm)	
Mounting Support	Mounting plate fixing bracket Upright fixing bracket	
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SD Spacial Spacial SMX Spacial Spacial SDX	
Device Composition	2 upright	
Quantity Per Set	Set of 1	
Material	steel	

Complementary

Surface Finish	Zinc coated	
Adjustment	Adjustable in depth every 25 mm with caged nuts Adjustable in height every 2.5 mm with quarter-turn nuts	
Height	55.12 in (1400 mm) Real 50.20 in (1275 mm)	
Width	1.77 in (45 mm)	
Depth	1.34 in (34 mm)	
Thickness	0.08 in (2 mm)	
Cut-Out Dimensions	13 x 11 mm	

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480148729
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

9		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.38 in (3.5 cm)	
Package 1 Width	2.36 in (6 cm)	
Package 1 Length	50.39 in (128 cm)	
Package 1 Weight	8.40 lb(US) (3.81 kg)	
Unit Type Of Package 2	PAM	
Number Of Units In Package 2	40	
Package 2 Height	19.69 in (50 cm)	
Package 2 Width	Width 39.37 in (100 cm)	
Package 2 Length	47.24 in (120 cm)	
Package 2 Weight	363.76 lb(US) (165 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations