Specifications



Set of 2 heavy duty vertical rails for fixing of chassis and cross rails-1200 mm

NSYTVR12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 172.20 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Technical upright
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 47.24 in (1200 mm)
Mounting Support	Mounting plate fixing bracket Upright fixing bracket
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	2 upright
Quantity Per Set	Set of 1
Material	steel

Complementary

Surface Finish	Zinc coated
Adjustment	Adjustable in depth every 25 mm with caged nuts Adjustable in height every 2.5 mm with quarter-turn nuts
Height	47.24 in (1200 mm) Real 42.32 in (1075 mm)
Width	1.77 in (45 mm)
Depth	1.34 in (34 mm)
Thickness	0.08 in (2 mm)
Cut-Out Dimensions	13 x 11 mm

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480148712
Returnability	No
Country Of Origin	FR

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	2.36 in (6.0 cm)
Package 1 Length	42.52 in (108.0 cm)
Package 1 Weight	7.14 lb(US) (3.24 kg)
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	100
Package 2 Height	19.69 in (50.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	742.96 lb(US) (337.0 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations