



Plastic window with hinged transparent cover, L78xW235xD25mm.

NSYVA2712MA

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 12.02 USD

Main

Range	Thalassa
Accessory / Separate Part Category	Installation accessory
Product Or Component Type	Window
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Range Compatibility	Thalassa Thalassa PLA Thalassa Thalassa PLM Spacial Spacial S3D Spacial Spacial CRN Thalassa Thalassa PLS
Accessory / Separate Part Destination	For modular device
Mounting Location	Installation on door or panel
Device Composition	1 complete window
Material	Transparent polycarbonate
Lock Type	Possibility to seal it Lock without key
Total Number Of 18 Mm Modules	12

Complementary

Height	3.07 in (78 mm)
Width	9.25 in (235 mm)
Depth	0.98 in (25 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480185243
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of	Package 1	PCI
--------------	-----------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	10.24 in (26 cm)
Package 1 Width	3.94 in (10 cm)
Package 1 Length	1.18 in (3 cm)
Package 1 Weight	19.84 lb(US) (9 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	400
Package 2 Height	47.24 in (120 cm)
Package 2 Width	31.50 in (80 cm)
Package 2 Length	41.34 in (105 cm)
Package 2 Weight	185.19 lb(US) (84 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations