

Product data sheet

Specifications



Stainless canopy 304L, Scotch Brite® finish. for WM enclosure W250xD150mm

NSYTX2515

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 489.45 USD

Main

| | |
|------------------------------------|-----------------------------|
| Range | Spacial |
| Accessory / Separate Part Category | Enclosure accessory |
| Product Or Component Type | Canopy |
| Application | Multi-purpose |
| Range Compatibility | Spacial Spacial S3X |
| For Enclosure Nominal Dimensions | - |
| Mounting Location | On top of enclosure |
| Device Composition | 1 canopy fixing elements |

Complementary

| | |
|------------------|-----------------------|
| Quantity Per Set | Set of 1 |
| Material | stainless steel 304L |
| Surface Finish | Scotch-Brite® brushed |
| Fixing Mode | By fixing element |
| Height | 2.01 in (51 mm) |
| Width | 10.04 in (255 mm) |
| Depth | 7.20 in (183 mm) |
| Thickness | 0.04 in (1 mm) |
| Net Weight | 1.94 lb(US) (0.88 kg) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US10ES180036 |
| Discount Schedule | 0ES1 |
| Gtin | 3606480156199 |
| Returnability | No |
| Country Of Origin | BG |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-------------------------|
| Package 1 Height | 3.15 in (8.0 cm) |
| Package 1 Width | 7.87 in (20.0 cm) |
| Package 1 Length | 10.63 in (27.0 cm) |
| Package 1 Weight | 31.04 oz (880.0 g) |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 60 |
| Package 2 Height | 16.93 in (43.0 cm) |
| Package 2 Width | 39.37 in (100.0 cm) |
| Package 2 Length | 47.24 in (120.0 cm) |
| Package 2 Weight | 145.06 lb(US) (65.8 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|------------------------------------------------------------------------------------------------------------------------|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |